

Technical Information

FieldEdge SGC500

Industrial edge device for connecting field devices to the Netilion Cloud



Application

- Enables the connection of field devices in an industrial plant to the Netilion Cloud.
- Data transmission is via the Internet connection in the plant.
- Information required for Netilion Services is regularly read out of the field devices and saved in Netilion.

Your benefits

- Connects field devices to the Netilion Cloud.
- Secure data transfer via encrypted https communication.
- Transmission of device parameters from connected field devices – Endress+Hauser devices and third-party devices.
- Easy installation and commissioning.
- No integration into customer automation system necessary.

About this document

Symbols

Safety symbols

DANGER

This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.

WARNING

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in serious or fatal injury.









CAUTION

This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in minor or medium injury.

NOTICE

This symbol contains information on procedures and other facts which do not result in personal injury.

Symbols for certain types of information

Symbol	Meaning
	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
	Forbidden Procedures, processes or actions that are forbidden.
	Tip Indicates additional information.
	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.

Function and system design

Function

The FieldEdge SGC500 enables the connection of field devices in an industrial plant to the Netilion Cloud. Data transmission is via the Internet connection in the plant. The information required for Netilion Services is regularly read out of the field devices and saved to the Netilion Cloud.

You can use the transmitted data via the following offers:

- Netilion Connect or
- Netilion Services

Netilion Connect

The transmitted data can be retrieved directly via a software interface (REST JSON Application Programming Interface (API)) and integrated into a user application.




The Application Programming Interface (API) is provided as part of the Netilion Connect Subscription.

Netilion Services

The transmitted data enable digital Netilion Services, such as Analytics, Health, Library and Value.

System design



1 Network architecture

- 1 Endress+Hauser field devices and third-party field devices
- 2 Fieldbus communication
- 3 Supported field gateways for conversion from fieldbus protocol to an IP protocol
- 4 Ethernet communication
- 5 FieldEdge SGC500, reads field device data and transmits it securely to the Netilion Cloud
- 6 WAN Internet connection – https, plant-side connection
- 7 Netilion Cloud
- 8 https Internet connection
- 9 Netilion Services: Netilion Service app based on internet browser
- 10 User application
- 11 Netilion Connect: Application Programming Interface (API)
- 12 Industrial Ethernet

- For detailed information on Netilion Connect, see: <https://developer.netilion.endress.com/discover>
- For detailed information on Netilion Services, see: <https://netilion.endress.com>

Communication and data processing

Supported fieldbus communication	Connection to FieldEdge
HART	Fieldbus via field gateway to Ethernet connection
WirelessHART	
PROFIBUS	
EtherNet/IP	Direct via industrial Ethernet connection

FieldEdge	Connection to the Netilion Cloud
FieldEdge SGC500	Internet connection: WAN – https

Power supply

Supply voltage

- Supply voltage: 9 to 36 V_{DC}
- Recommended: 24 V_{DC}

Power consumption

20 W

Electrical connection	<p>Front</p> <ul style="list-style-type: none"> ▪ ON switch ▪ 4 × USB 3.0 port (not used) ▪ 1 × 3 pin CAN bus (not used) ▪ 1 × 8 Bit Isolated Digital I/O (not used) ▪ 1 × audio jack (line-out; mic-in)(not used) <p>Top</p> <ul style="list-style-type: none"> ▪ 2 × RS-232/422/485 COM ports (not used) ▪ 9 to 36 V_{DC} power supply <p>Bottom</p> <ul style="list-style-type: none"> ▪ 2 × display port (not used) ▪ 3 × GbE-LAN-Port (LAN 2 not used)
------------------------------	---

Performance characteristics

Hardware	<p>CPU Intel Atom x5-E3930 dual core</p> <p>Storage 4 GB LPDDR4 onboard memory</p> <p>Integrated graphics card Intel HD Graphics 500 (not used)</p>
-----------------	--

Environment

Ambient temperature range	-25 to 70 °C (-13 to 158 °F)
----------------------------------	------------------------------

Storage temperature	-40 to 85 °C (-40 to 185 °F)
----------------------------	------------------------------

Humidity	0 to 90 %, non-condensing
-----------------	---------------------------

Vibration resistance	<p>Tested acc. to</p> <ul style="list-style-type: none"> ▪ IEC 60068-2-64 ▪ MIL-STD-810G
-----------------------------	--

Shock resistance	<p>Tested acc. to</p> <ul style="list-style-type: none"> ▪ IEC 60068-2-27 ▪ MIL-STD-810G
-------------------------	--


Electromagnetic compatibility (EMC)	<ul style="list-style-type: none"> ▪ CE Declaration of Conformity ▪ Low Voltage Directive (2014/35/EU) ▪ EN 62368-1:2014 / A11:2017 ▪ Electromagnetic compatibility (2014/30/EU) ▪ EN 55024:2010 ▪ EN 55032:2015/AC:2016 Class A ▪ EN 61000-3-2:2014 Class D ▪ EN 61000-3-3:2013 ▪ EN 61000-4-2:2009 ▪ EN 61000-4-3:2006+A1:2008+A2:2010 ▪ EN 61000-4-4:2012 ▪ EN 61000-4-5:2014+A1:2017 ▪ EN 61000-4-6:2014+AC:2015 ▪ EN 61000-4-8:2010 ▪ EN 61000-4-11:2004+A1:20 ▪ EN 55035:2017 ▪ EN 301 489-1 V2.2.0 (2017-03) Draft
--	--

- EN 301 489-17 V3.2.0 (2017-03) Draft
- RoHS 3 (2015/863/EU)
- EN 63000:2018
- WEEE (2012/19/EU)
- EN 50419:2006
- EN 50625-1:2014

Mechanical construction

Design, dimensions

56 mm (2.20 in) · 154 mm (6.06 in) · 119 mm (4.69 in)



 2 Dimensions of SCG500, engineering unit: mm (in)

 Sufficient space around the SGC500 is required for heat dissipation.

Certificates and approvals

CE mark

The SGC500 meets the requirements of the EU Directives as per the CE mark.

Other standards and guidelines

- FCC & Canada ISED DoC
 - CE EMC, Safety, RoHS 3.0 DoC
 - UL listing card
 - CB certificate
- Detailed list:**
- FCC 47 CFR Part 15
 - UL-listed configurations available
 - CB schematics
 - EN 55024
 - EN 55032
 - EN 62368-1
 - 2011/65/EU (RoHS 2 Directive)
 - WEEE Directive (2012/19/EU)
 - IEC 60068-2-27
 - IEC 60068-2-64

Ordering information



For detailed information on using the SGC500, see www.netilion.endress.com.

Detailed information on the product structure are available as follows:
From your Endress+Hauser Sales Center: www.addresses.endress.com



- For detailed information on Netilion Connect, see:
<https://developer.netilion.endress.com/discover>
- For detailed information on Netilion Services, see:
<https://netilion.endress.com>

Scope of delivery

The scope of delivery comprises:

- SGC500
- 1 × power terminal block connector
- 1 × fastening clip for DIN rail mounting
- 1 × dust protection cap
- 1 × documentation

Registered trademarks

PROFIBUS® is a registered trademark of the PROFIBUS User Organization, Karlsruhe/Germany.

HART®, WirelessHART® is the registered trademark of the FieldComm Group, Austin, TX 78759, USA.

EtherNet/IP™ is a trademark of ODVA, Inc.



www.addresses.endress.com
